

Lotus

LED Line Light

Supplementary Information for LOTUS LED Line Light at Longer Working Distances (WD) i.e. > 200mm



LOTUS is available in a range of optical configurations: L1, D1, F1 and B1. For Working Distances >200mm ProPhotonix recommend L1 & D1 configurations.

Optical Configuration

F1: 30° x 4° diffuser


B1: 60° diffuser

L1: Collimating lens

D1: Collimating lens
+ F1 Diffuser

WHITE LOTUS LED Line Light

Beam Width Versus Working Distance



Intensity versus Working Distance

